

Interface module - VIP-2/SC/D37SUB/M/SO - 2900786

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




VARIOFACE module, with screw connection and male D-Subminiature pin strip, for mounting on NS 35 rails, 37-pos.

Why buy this product

- These VARIOFACE modules are used in combination with the relevant front adapters



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 545082
Weight per Piece (excluding packing)	211.9 g
Custom tariff number	85369010
Country of origin	United States
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width	101 mm
Height	65.5 mm
Depth	45.1 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. permissible operating voltage	125 V AC/DC
Max. perm. current (per branch)	2 A
Number of positions	37
Status display	No

Interface module - VIP-2/SC/D37SUB/M/SO - 2900786

Technical data

General

Mounting position	any
Standards/regulations	DIN EN 50178

Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max.	12
Stripping length	8 mm
Screw thread	M 3

Connection data for connection 2

Connection name	D-SUB connection
Number of connections	1
Connection method	D-SUB pin strip
Number of positions	37

Supported controller

Controller	HONEYWELL C300
- suitable I/O card	TDIL01 (non-redundant)
	TDOB01 (non-redundant)
	TAOX01 (non-redundant)
	TAIX01 (non-redundant)
	TDIL11 (redundant)
	TDOB11 (redundant)
	TAOX11 (redundant)
	TAIX11 (redundant)

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152

Interface module - VIP-2/SC/D37SUB/M/SO - 2900786

Classifications

eCl@ss

eCl@ss 8.0	27141152
------------	----------

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Drawings

