

## RefLED+ ES50

RefLED+ ES50 V2 380Lm DIM 4000K 40d

0026819

### Range features



### PRODUCT OVERVIEW

Light colour	840 Cool White
Ordering number	0026819
Technology	LED
Average life (Rated) (h)	25000
Energy class	A+
Lamp finish	Silver
Lamp shape	Reflector
Dimmable	Yes
Cap/Base	GU10
Type	RefLED+ ES50
EAN code	5410288268194
CRI (Ra)	80
Beam angle(°)	40
Colour temperature (K)	4000
Useful luminous flux (Rated) (lm)	380
Efficacy (Rated) (lm/w)	69.09
Watt (Nominal) (W)	5.5
Equivalent watt (W)	55
Voltage (V)	220-240

# RefLED+ ES50

RefLED+ ES50 V2 380Lm DIM 4000K 40d

**0026819**

## DATA TABLE

### General data

Ordering number	0026819
Technology	LED
Average life (Nominal) (h)	25000
Energy class	A+
Average life (Rated) (h)	25000
Lamp shape	Reflector
Lamp finish	Silver
Dimmable	Yes
Cap/Base	GU10
Type	RefLED+ ES50
EAN code	5410288268194
Product name	RefLED+ ES50 V2 380Lm DIM 4000K 40d
Lamp mercury content (mg)	0
Starting time (max) (s)	<0,5
Warm-up time to 60% of full light (max) (s)	< 1s => 95%
Control gear required	No
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	100000
Special purpose lamp	No
Transformer required	No
Optimal operating condition (°C)	25

### Optical data

Light colour	840 Cool White
CRI (Ra)	80
Beam angle(°)	40
Colour temperature (K)	4000
Useful luminous flux (Rated) (lm)	380
Lumen maintenance at end of nominal life (%)	70
Luminous flux (Nominal) (lm)	380
Peak intensity (cd)	745
Adjustable chromaticity	No

### Electrical data

kWh per 1000 hours burning time	6
Efficacy (Rated) (lm/w)	69.09
Watt (Rated) (W)	5.5
Watt (Nominal) (W)	5.5
Equivalent watt (W)	55
Voltage (V)	220-240
Lamp power factor	0.8

## RefLED+ ES50

RefLED+ ES50 V2 380Lm DIM 4000K 40d

**0026819**

### Physical data

Lamp Length (mm) - C/L	55.5
Max. Lamp Diameter (mm) - D	50
Lamp dimension equal to filament lamp equivalent	Yes
Designed for optimum use in non standard conditions	No
Fluorescent lamp replacement	No

### ENERGY LABEL

