

## Docking frames - HC-B 24-ANDOCK - 1586141

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Docking frame for racks, for contact inserts of B24 type, with four M5 flat headed screws, rack balance x/y axis +/- 1.5 mm



### Key commercial data

Packing unit	1 pc
GTIN	4 046356 345750
Weight per Piece (excluding packing)	125.2 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### General

Material	Stainless steel
----------	-----------------

### Classifications

#### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27189207
eCl@ss 5.1	27189207
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209

#### ETIM

ETIM 3.0	EC002310
ETIM 4.0	EC002310
ETIM 5.0	EC002310

# Docking frames - HC-B 24-ANDOCK - 1586141

## Classifications

### UNSPSC

UNSPSC 6.01	30211817
UNSPSC 7.0901	39121416
UNSPSC 11	43172601
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

## Approvals

### Approvals

Approvals

EAC

Ex Approvals


Approvals submitted

### Approval details

EAC
-----


## Drawings

Dimensioned drawing



Dimensional drawing


Dimensioned drawing



Panel cutout

## Docking frames - HC-B 24-ANDOCK - 1586141

Dimensioned drawing



max. dimensions of both the docking frames (in case of standard contacts 25.8 mm; in case of fiber optics contacts 27 mm; in case of pneumatic contacts 26.5 mm)