





NUMBER C-174465



METRIC

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST



注 ;

- △ -Z- 面より2mmの範囲で測定。
- 2.内装するタブコンタクト型番173630,173631.
- 3.嵌合相手ハウジング型番174468

NOTE:

- △ MUST BE KEPT BETWEEN -A- AND 2.
- 2.APPLIED TAB CONTACT P/N; 173630,173631.
- 3.APPLIED PLUG HSG P/N; 174468

オレンジ (ORANGE)	174465-8
黄 (YELLOW)	174465-7
灰 (GRAY)	174465-6
青 (BLUE)	174465-5
緑 (GREEN)	174465-4
黒 (BLACK)	174465-2
白 (WHITE)	174465-1
色 (COLOR)	型番 (PART NUMBER)

OBSOLETE

				Copyright ©1989年 AMP (Japan) LTD. ALL RIGHTS RESERVED.		Copyright ©1989 AMP (Japan) LTD. ALL RIGHTS RESERVED.		AMP Tyco Electronics AMP K.K.	
				WIRE RANGE mm ² (AWG)	INSULATION DIA mm	NAME .070シリーズ マルチロック I/Oコネクタ 10極 プラグハウジング .070SERIES MULTILOCK I/O CONNECTOR, 10Pos. PLUG HOUSING			
				MATERIAL PBT	FINISH ---	GENERAL TOLERANCE		LOC B J	NUMBER C-174465
				D1 OBSOLETE -4 FJ00-0279-99 AY KB 29FEB 90	DR DE 6/29'94 6/29'94		0<X<10 : ±0.2 10<X<30 : ±0.25 30<X<100 : ±0.3 ANGLES : ±3°		SCALE 2-1
				D CHANGE LETTER FJ00-0599-98 KS SI 27MAR 98	DR DE 6/30'94 6/30'94		REV. D1		SHEET #
				C 再作成 & 色追加 FJ00-0854-94 HK KA 6/30'94	CHK. APP. 6/30'94 6/30'94				
LTR REVISION RECORD				DR	CHK	DATE			