

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [15-31-1033](#)
Status: **Active**
Description: 4.80mm Pitch Wire-to-Wire Plug Housing, 3 Circuits

Documents:

3D Model	Product Specification PS-5025-002 (PDF)
Drawing (PDF)	Product Specification PS-5025-003 (PDF)
Product Specification PS-5025-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	5025
Application	Power, Wire-to-Wire
Product Name	N/A
UPC	800753684287

Physical

Circuits (maximum)	3
Flammability	94V-2
Gender	Male
Glow-Wire Compliant	No
Net Weight	1270.700/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.80mm
Pitch - Termination Interface	4.80mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Material Info

Old Part Number	5025-03P1
-----------------	-----------

Reference - Drawing Numbers

Product Specification	PS-5025-001, PS-5025-002, PS-5025-003
Sales Drawing	SD-5025-03P*

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[5025Series](#)

Mates With
[5025](#) Receptacle

Use With
[5006](#)