

Datasheet

RS 25 Core Screened Industrial Cable, PVC Sheath, 6.3mm OD, 0.055 mm² CSA 0.25 A, 300 V, 25m

RS Stock number 660-0413



Electrical Characteristics

Max. Conductor DC Resistance at 20°C (Ω /km)	<345
Rated Temperature (°C)	-20 to +80
Rated Voltage (V)	300
20°C Insulation Resistance (M Ω .km)	> 200

