



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCKY
Product compatibility	XCKJ
Associated head	ZCKE05
Movement of operating head	Rotary
Type of operator	Roller lever spring return thermoplastic (-)
Type of approach	Lateral approach

Complementary

Switch actuation	By 30° cam
Positive opening	With

Environment

Ambient air temperature for operation	10...120 °C for high temperature
Ambient air temperature for storage	10...120 °C for high temperature
Environmental characteristic	High temperature

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1440 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations