



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		H2	REVISED PER ECO-11-004587	11MAR11	RK	HMR





PERIPHERAL SEAL
BONDED IN PLACE
SEE TABLE

A HOLE
4 PLC

FLANGED



FREE HANGING



RECOMMENDED PANEL CUTOUT
SCALE 2:1

STANDARD	YES	4-40 BRASS THREADED INSERT	20	FLANGED	206433-6
SMALL PACK	NO	.125 DIA	20	FLANGED	206433-5
STANDARD	NO	.125 DIA	20DF WITHOUT INSULATION SUPPORT	FLANGED	5 206433-4
STANDARD	NO	4-40 BRASS THREADED INSERT	20	FLANGED	206433-3
STANDARD	NO	-	20	FREE HANGING	206433-2
STANDARD	NO	.125 DIA	20	FLANGED	206433-1
PACKAGING	PERIPHERAL SEAL	A	WILL ACCEPT SOCKET CONTACT SIZE	TYPE	PART NUMBER

- 1 CONTACT CAVITIES IDENTIFIED BY CHARACTERS ON FRONT AND REAR FACE.
- 2 AMP MOLDED ON THIS SURFACE.
- 3 PART NUMBER AND DATE CODE MARKED ON THIS SURFACE.
- 4 206433-4 STRIPPED WIRE LENGTH SHOULD BE .193-.213 WITH .095 MAX INSULATION.
- 5 OBSOLETE PART NUMBER.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
NYLON, GLASS FILLED,
FLAME RETARDED, BLACK

FINISH
-

DWN
J.McCLINTON
1-25-88

CHK
R.STONE
1-26-88

APVD
M.KAPEZYNSKI
1-27-88

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

FINISH
-

TE Connectivity

RECEPTACLE ASSEMBLY,
ARRANGEMENT 11-8
REVERSE SEX, CPC

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-206433

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 1

REV
H2