

DIECAST AND METAL BOXES

5000 Series Multi-Purpose Diecast - NEW COLOURS

Highly durable robust aluminium diecast boxes with RFI shielding properties.

- Diecast aluminium
- Lid mounted by four M3 machine screws
- Temperature resistant up to 260°C (without gasket)
- Highly Durable and shock resistant
- Vertical guides for PCB fixing
- Optional neoprene gasket for IP65 seal

SPECIFICATION	
Materials	Lid & base diecast aluminium to ENAC 44200
Protection class	IP54 IP65 optional
Standard colours	Red, yellow, blue and green Base, lid & x4 zinc plated M3 screw
Standard unit includes	Wall mounting kit
Options	IP65 gasket

RED	YELLOW	BLUE	GREEN	LENGTH	WIDTH	HEIGHT
RTM5001/11-RED	RTM5001/11-YEL	RTM5001/11 - BLU	RTM5001/11 - GRN	50mm	50mm	31mm
RTM5002/12-RED	RTM5002/12-YEL	RTM5002/12 - BLU	RTM5002/12 - GRN	101mm	50mm	25mm
RTM5003/13-RED	RTM5003/13-YEL	RTM5003/13 - BLU	RTM5003/13 - GRN	112mm	62mm	31mm
RTM5004/14-RED	RTM5004/14-YEL	RTM5004/14 - BLU	RTM5004/14 - GRN	120mm	66mm	40mm
RTM5005/15-RED	RTM5005/15-YEL	RTM5005/15 - BLU	RTM5005/15 - GRN	152mm	82mm	50mm
RTM5006/16-RED	RTM5006/16-YEL	RTM5006/16 - BLU	RTM5006/16 - GRN	192mm	112mm	61mm
RTM5007/17-RED	RTM5007/17-YEL	RTM5007/17 - BLU	RTM5007/17 - GRN	121mm	95mm	61mm

