




ball nosed cylinder

Walzenrundform
cylindrique bout rond
cilindro esférico



	2.5	3	3	3	4	5	6	6	6	8	10
d1 mm	2.5	3	3	3	4	5	6	6	6	8	10
l1 mm	11	13	13	13	16	16	13	19	25	19	19
d2 mm	3	3	3	3	6	6	3	6	6	6	6
l2 mm	38	38	50	75	50	50	45	50	50	65	65
s	T3100	T3200	-	-	T3300-6	-	T3240	T3400	-	T3500	T3600
d	T3100D	T3200D	T3200DL	T3200DL	T3300D-6	T3350D-6	T3240D	T3400D	T3400D-1	T3500D	T3600D
d-max	-	-	-	-	-	-	-	-	-	TDX350	TDX360
c	-	T3200C	-	-	-	-	-	T3400C	-	-	T3600C
k	-	T3200K	-	-	T3300K-6	-	-	T3400K	-	T3500K	T3600K
alu	-	-	-	-	-	-	-	TTA340	-	-	TTA360
I.S.O. Ref.	-	C031303	C031303	C031303	C041606	C061606	C061303	C061906	C062906	C081906	C101906
SCTI Nr.	SC-41M	SC-42M	SC-42ML2	SC-42ML3	SC-13M	SC-14M	SC-51M	SC-1M	SC-1ML	SC-2M	SC-3M