



Ty-Fast®

TY400-50

All-plastic cable tie for multi purpose use.

T&B Catalog Number: TY400-50
EAN Number: 05414363064602
UPC Number: 78621089854
Description: All-plastic, standard cable tie, 366 x 4.6 mm, natural Polyamide 6.6



Technical Information

| | |
|---------------------|----------------|
| Type | standard |
| Material | Polyamide 6.6 |
| Temperature Range | -40°C to +85°C |
| Flammability Rating | UL 94 V-2 |
| Colour | natural |
| Halogen free | yes |
| Silicone free | yes |

Approvals

| | |
|-----------------------------|-----------|
| UL recognised | E49405 |
| Germanischer Lloyd approval | yes |
| Lloyds Register approval | yes |
| MIL Spec. | MS-3367-2 |
| Other approval | BVQ |

Ordering Information

| | |
|---------------------------|------|
| Length (mm) | 366 |
| Width (mm) | 4.6 |
| Max. Bundle Diameter (mm) | 102 |
| Min. Bundle Diameter (mm) | 1.6 |
| Min. Tensile Strength (N) | 220 |
| Quantity (pieces) | 1000 |
| Packaging Type | bag |

Storage Conditions

Nylon (Polyamide) is inherently susceptible to environmental conditions. Polyamide 6.6 cable ties are moisturised to optimum performance levels at machine-side and should be stored in cool dry areas out of direct sunlight. Cable ties are packaged in plastic bags to contain moisture and should remain sealed until ready for use.

Tooling

ERG50, ERG120, WT193A
