







SPECIFICATIONS

Voltage rating : 250V AC/DC
Current rating : 7A AC/DC
Withstanding voltage : 1500V AC/minute
Contact resistance : 20m Ω max
Temperature range : -40°C to +105°C
Insulation resistance : 1000M Ω min

MATERIAL

Insulator : Nylon66 (UL94V-2)
Insulator color : Transparnt White
Contact : Brass
Plating : Tin Plated

Poles	Dimensions(mm)	
	A	B
2	-----	5.60
4	4.20	9.80
6	8.40	14.00
8	12.60	18.20
10	16.80	22.40
12	21.00	26.60
14	25.20	30.80
16	29.40	35.00
18	33.60	39.20
20	37.80	43.40
22	42.00	47.60
24	46.20	51.80

TOLERANCE (mm)		APPROVALS		DATE	TITLE	AMPHENOL Amphenol European Design Center	
X.	± 0.3	DRAWN	Stephane	05/Jan/2007			
XX	± 0.2	CHECKED	Rob	05/Jan/2007			
X.XX	± 0.15	APPROVED	Rob	05/Jan/2007			
UNLESS OTHERWISE SPECIFIED				UNIT : mm	SIZE : A4	DRAWING N°	REV. A

4.2 Power Wafer
R/A Dip

Scale N.A. Sheet 1 of 1

MF42-RD-XX