

## Datasheet

### Blue 30m Nylon Air Hose, -40 → +80°C, Application Various

RS Stock number [483-4936](#)



## Product Details

### Standard Nylon Tube

Suitable for most pneumatic requirements in or out of the control cabinet. Available in 6 colours

Suitable for use with pneumatic fittings

Manufactured to BS 5409 (part 1) 1976- IS07628/1

Maximum working pressure =>21 bar

Burst pressure =>63 bar

Operating temperature range -40 to 80°C

30m coils

RS, Professionally Approved Products, gives you professional quality parts across all product categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

### Note

Stock 4835557 - Bend Radius 35mm

### Push-in System - Nylon Tube

All coils shown are non anti-static.