

Cable - CABLE-50/4FLK14/22,0M/YUC - 2902800

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled round cable with a 50-pos. molded socket strip and four 14-pos. socket strips, for splitting 32 channels into 4 x 8 channels. Number of positions: 50/4 x 14. The cable is suitable for cards ADV551 and ADV151. Cable length: 22.0 m

Why buy this product

- Four 14-pos. connectors on the module side for connecting four 8-channel VARIOFACE modules of the system cabling
- Lateral cable outlet of the I/O module



Key commercial data

Packing unit	1
GTIN	 4 046356 681025
Custom tariff number	85444290

Technical data

General

Nominal voltage U_N	30 V DC
Max. current carrying capacity per path	500 mA (Up to 55°C ambient temperature)
Max. conductor resistance	0.16 Ω /m
Length of cable	22 m
Single wire, cross section	0.14 mm ²
AWG	26
Conductor construction: Number of litz wires:	7
External diameter	11 mm
Shielding	no
Outer sheath, material	PVC
External sheath, color	Gray RAL 7035

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Flame resistance	IEC 60332-1

Cable - CABLE-50/4FLK14/22,0M/YUC - 2902800

Technical data

Environmental conditions

Resistance to oil	DIN VDE 0472 Part 803, test type B
Gasoline resistance	Against occasional splashes

Connector, module side

Number of positions	14
Connectors	IDC/FLK socket strip (2.54 mm)
Number of plugs	4

Connector, controller side

Number of positions	50
Connectors	IDC/FLK socket strip (2.54 mm)
Number of plugs	1

Connection data

Connection method	Screw connection
Torque	0.5 Nm

Supported controller

Controller	YOKOGAWA CENTUM CS3000R3
- suitable I/O card	ADV151
	ADV551
Controller	YOKOGAWA STARDOM
- suitable I/O card	NFDV151
	NFDV551

Classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27249205

ETIM

ETIM 3.0	EC000237
ETIM 4.0	EC000237
ETIM 5.0	EC000237

UNSPSC

UNSPSC 6.01	26121620
-------------	----------

Cable - CABLE-50/4FLK14/22,0M/YUC - 2902800

Classifications

UNSPSC

UNSPSC 7.0901	26121620
UNSPSC 11	26121620
UNSPSC 12.01	26121620
UNSPSC 13.2	26121620

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Drawings

Cable - CABLE-50/4FLK14/22,0M/YUC - 2902800

Connection diagram

50-pos. connector to the I/O card	4 x 14-pos. connector to the module	Wire color
50	1	black
49	3	brown
48	5	red
47	7	orange
46	9	yellow
45	11	green
44	13	blue
43	15	violet
42	44	gray
41	39	white
40	17	white-black
39	19	white-brown
38	21	white-red
37	23	white-orange
36	25	white-yellow
35	27	white-green
34	29	white-blue
33	31	white-violet
32	43	white-gray
31	37	brown-black
30	2	brown-red
29	4	brown-orange
28	6	brown-yellow
27	8	brown-green
26	10	brown-blue
25	12	brown-violet
24	14	brown-gray
23	16	brown-white
22	42	green-black
21	36	green-brown
20	18	green-red
19	20	green-orange
18	22	green-blue
17	24	green-violet
16	26	green-gray
15	28	green-white
14	30	yellow-black
13	32	yellow-brown
12	41	yellow-red
11	34	yellow-orange