

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19433-0013

Status:

Active

Overview:

MX150L™ Industrial Sealed Connector System

Description:

MX150L™ 2 Circuit Plug for 10-12 AWG Wire



Documents:

3D Model

Drawing (PDF)

Product Specification PS-19432-001 (PDF)

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification	
CSA	LR18689
UL	E152602
General	
Product Family	Crimp Housings
Series	19433
Application	Power, Wire-to-Wire
Comments	Mat Seal Color is Yellow, Polarized to Mating Part. IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector S
Overview	MX150L™ Industrial Sealed Connector System
Product Literature Order No	987650-2181
Product Name	MX150L™
UPC	822350190886
Physical	
Circuits (maximum)	2
Circuits Detail	1x1
Flammability	94V-0
Gender	Male
Glow-Wire Compliant	No
Keying to Mating Part	N/A
Lock to Mating Part	Yes
Net Weight	14.062/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C
Electrical	
Current - Maximum per Contact	30A
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-19432-001
Sales Drawing	SD-19433-001

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19433Series

Mates With

19432-0013 Female Receptacle

Use With

19431 Male Terminal

This document was generated on 10/09/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION