



mecalectro

Small linear solenoid for intensive use – 8.55.AA.62



Stroke: 5 mm

Force at beginning of stroke (FM: 100/25/5%):
2/5/12.5 N

Force at end of stroke (FM: 100/25/5%):
5.5/14.5/20 N

Power Consumption (FM: 100/25/5%):
7.5/25/96 W

Total mass: 100 g

Degree of protection / Energetic class: IP 40 / B
Standard supplies: 24Vcc

Possible supplies: From 12 to 180Vcc

Duty Cycle: Permanent, impulsions (100 / 40 / 25 / 15 / 5 %)

Standard: NF C 79300

Examples of applications: Automats, electrical equipment, machinery, security applications.