



ENGLISH

Datasheet

RS Pro Clear 5m Long Coil Tubing Without Connector Fluoropolymer 12 bar, -40 → +150°C

RS Stock No: **486-8945**



Product Details

RS Pro coil tubing without connector is suitable for a temperature range of -40 to +150°C. This clear tubing withstands pressure up to 12 bar. It is highly resistant to aggressive and corrosive agents.

Features and Benefits

- PTFE tubing with high resistance to aggressive and corrosive agents
- High abrasion resistance
- Meets requirements of FDA 177.1550
- Temperature range: -40 to +150°C

**Specifications:**

Colour	Clear
Material	Fluoropolymer
Special Features	PTFE Tubing with High Resistance to Aggressive & Corrosive Agents, High Abrasion Resistance
Maximum Operating Length	5 m
Maximum Operating Temperature	+150°C
Minimum Operating Temperature	-40°C
Tube Inside Diameter	8 mm
Tube Outside Diameter	10 mm
Maximum Operating Pressure	12 bar