



fitted with

work equipment
connected load
power consumption
system of protection
class of protection
usage
luminaire body

lamp cover
tubular sections
balance of articulation joints
weight (net)
mains supply

fastening

1 x halogen lamp QT12 60W PK22s 24V
light colour warm white, 3000 K, Color Rendering Index (CRI)=100
without
24 V; AC/DC
approx. 56 W
IP 54
III
switch
sectional aluminium, anodised, aluminium coloured
anodised
glass screen
steel tube, painted, silver
friction
approx. 2.5 kg
connector
2-polig
screw-down flange, table clamp (accessory), wall bracket (accessory)



2-polig

illuminance

measuring conditions: 50

Em: 3341 lx
Emax: 27230 lx
Emin: 221 lx

