



Bottled Water System Plus

FOR HOME AND COMMERCIAL APPLIANCES

The NEW Eco-Friendly Bottled Water System Plus is part of Flojet's premium water dispensing product line.

When a water bottle is connected to the system, fresh water is available for use with coffee/tea machines, water dispensers, refrigerators, ice makers, or any other application where portable potable water is needed.

The Bottled Water System Plus is also designed for convenience – the pump shuts off when the water source is depleted, and when water is restored, the pump will automatically restart. This eliminates the chance of any damage to the pump and control box from running dry.

Features and Benefits

- **Illuminated On/Off Switch:** Provides clear visibility in dark cabinets or hard to reach places
- **Long Life Motor:** Ensures years of reliable operation
- **Flojet Diaphragm Pump:** Provides dependable run dry capabilities, extending the life of the pump
- **Quick Disconnect Port:** Allows for easy wand replacement in seconds
- **Quiet Operation:** Equipped with noise dampening rubber feet to minimize noise pollution
- **Thermal Protection:** Prevents overheating, protecting the pump and control box from damage
- **New Ergonomic T-Shaped Wand Handle:** Allows for ease of installation and removal of wand from bottle



Eco-Friendly

Up to 25% more energy efficient than previous bottled water systems

FLOJET
a xylem brand


Bottled Water System Plus

FOR HOME AND COMMERCIAL APPLIANCES




- Over the past 12 years, Flojet Bottled Water Systems have helped serve over two million cups of coffee per day in cafes and coffee shops worldwide
- Backed by the Flojet brand of electric diaphragm pump technology, a brand enjoying over 35 years of operational excellence
- Flojet's robust electric diaphragm pump design, proven with over seven million units in service
- Flojet Bottled Water Systems protect the environment by eliminating the need for a water filter when dispensing water to your refrigerator, preventing over 300,000 filters from being disposed of each year

Applications




Refrigerator Dispense



Coffee Maker Dispense

Dimensional Drawing



Wall Power Transformer


* Also available in EU, UK and AU power adapters.

Specifications

Flow Rate	1.10 GPM (4.10 LPM)
Max Pressure	40 PSI (2.76 bar)
Dimensions	2.7"H x 5.4"W x 8.5"D (6.86cm H x 13.72cm W x 21.60cm D)
Voltages	115 VAC, 230 VAC
Amp Draw	115 VAC, 0.5 amp max 230 VAC, 0.3 amp max
Cycles	50/60 Hz for AC models
Weight	4.5lbs (2.04kg)

Model Number	Voltage	Flow Rate	Max Pressure	Power adapter type
BW4000-000A	115 VAC	1.10 GPM (4.10 LPM)	40 psi (2.76 bar)	US Plug
BW4002-000A	230 VAC	1.10 GPM (4.10 LPM)	40 psi (2.76 bar)	AU Plug
BW4003-000A	230 VAC	1.10 GPM (4.10 LPM)	40 psi (2.76 bar)	UK Plug
BW4004-000A	230 VAC	1.10 GPM (4.10 LPM)	40 psi (2.76 bar)	EU Plug

Kit Includes



- A. Pump Module with On/Off Rocker Switch, 3.5ft (1m) Cord
- B. Suction Wand and Hose Assembly
- C. 20ft (6.1m) of 1/4in (6.35mm) Discharge Tube
- D. Kit Fitting: Hose port/connector, compression nut and sleeve
- E. Wall Transformer



Warranty: All products of the company are sold and all services of the company are offered subject to the company's warranty and terms and conditions of sale, copies of which will be furnished upon request. The information provided herein is for guidance only, it does not constitute a guarantee of the performance or specification of any individual product or component.

www.xylem.com

USA
Xylem, Inc.
17942 Cowan
Irvine, CA 92614
Tel (949) 608-3900
Fax (949) 609-3887

UK
Xylem, Inc.
Bingley Road, Hoddesdon
Hertfordshire EN11 0BU
Tel +44 (0) 1992 450145
Fax +44 (0) 1992 467132

GERMANY
Xylem, Inc.
Oststrasse 28
22844 Norderstedt
Tel +49-40-53 53 73-0
Fax +49-40-53 53 73-11

CHINA
Xylem, Inc.
30/F, Tower A Hongqiao City Center of Shanghai
100 Zunyi Road, Shanghai 200051, China
Tel +(86) 21 2208 2888
Fax +(86) 21 2208 2999

ITALY
Xylem, Inc.
Via Tommaseo, 6
20059 Vimercate, Milano
Tel +39 039 685 2323
Fax +39 039 666 307