

## Specification Grade 20 AMP Duplex GFCI Receptacle, Ivory

2095I



The most durable GFCI available with patented SafeLock™ Protection that ensures that if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected. Prevents line-load reversal miswire with no power to the face or downstream receptacles if wired incorrectly for added safety. Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.

### features & benefits

- **High-impact-resistant, thermoplastic construction** for superior strength and durability.
- **Captive screws** make for easier installation.
- **Extra-long strap for better sheet rock contact** eliminates "floaters" yet takes standard wall plate.
- **Back wire clamp** allows for fast installation of ground wires.
- **Trip indicator light (LED)** makes it easy to identify trip conditions.
- Side or internal screw-pressure-plate back wire with #10-#14 AWG solid or stranded copper wire.
- **Two back wire holes per terminal.**
- **Ground screw has a back wire clamp for easy installation.**
- **10kA short circuit rating.**
- **Mounting screws are shipped captive in the device and wall plate for easier installation.**
- **Extra-long strap.**
- **Button colors match the device face.**
- **Dual-direction test and reset buttons.**
- **Class A rated GFCI.**
- **Supplied with matching TP26 nylon wall plate.**
- **Tri-drive screws.**
- **10kA short circuit rating.**
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### specifications

#### General Info

Color: Ivory  
Available Colors: Ivory, White, Brown, Gray, Black, Red, Light Almond  
Type: Specification Grade  
Style: Decorator

### **Assembly/Installation Information**

Mounting Hardware Included: Yes

### **Listing Agencies/Third Party Information**

RoHS: No  
CSA Standard: C22.2 No. 42, 144  
CUL Listing No: E42190  
cULus: Yes  
cUL Standard: Yes  
Federal Spec: Yes  
Fed Spec Number: WC596  
UL Listing No: UL498  
UL Listed: Yes  
UL Standard: Yes  
UN SPS C: 39121614

### **Dimensions**

Depth U S: 0.98"  
Height U S: 4.2"  
Length U S: 4.20"  
Width U S: 1.72"

### **Technical Information**

Amps: 20A  
NEMA Configuration Number: 5-15R  
NEMA Rating: WD-1, WD-6  
Volts: 125V  
Volts A C: 125  
Grade Type: Specification

### **Buy American Act Compliance**

Country of Origin: CHINA  
Buy American Act Status: No