



Save as PDF



**SabreLite™ 2010 Recoil™ LED Flashlight**



The SabreLite 2010 LED is Peli's flagship LED light. LED Technology produces a white collimated beam that's as bright as an incandescent torch and provides 10,000 hours of lamp life and extended battery burn time. The rugged, light weight ABS resin body is submersible and a twist on/off lens shroud eliminates accidental discharge. It is powered by 3 C alkaline cells. The SabreLite 2010 light is the future of LEDs.



**Materials**

**SabreLite™ 2010 Recoil™ LED Flashlight**

**ANSI FL1 Specifications**

|                             |                             |
|-----------------------------|-----------------------------|
| <b>LIGHT SOURCE</b>         | High<br>LED                 |
| <b>BATTERIES</b>            | 3 C Alkaline (Not included) |
| <b>CHARGE TIME</b>          | N/A                         |
| <b>VOLTAGE</b>              | 4.5                         |
| <b>LENGTH</b>               | 20.6 cm (8.11")             |
| <b>WEIGHT W/ BATTERIES</b>  | 0.13 kg (4.5 oz.)           |
| <b>WEIGHT W/O BATTERIES</b> | 0.15 kg (5.36 oz.)          |

| Body | Lens                                      | Shroud                | Switch Type                 |
|------|---|-----------------------|-----------------------------|
| EXL  | Polycarbonate                             | ABS                   | Twist On/Off<br>Lens Shroud |
| Clip | Contact, Spring & Retainer                | O-Ring                | Night Vision Film           |
| ABS  | Stainless Steel and<br>Brass Nickel Plate | Ethylene<br>Propylene | N/A                         |

**Configuration**

| Cat. # | Description                            |
|--------|--|
| 2010   | SabreLite™ 2010 Recoil™ LED Flashlight |

**SabreLite™ 2010 Recoil™ LED Flashlight Accessories**

No accessories are currently available for this product

|                                      | FL 1 STANDARD | High   |
|--------------------------------------|---------------|--------|
| <b>LIGHT OUTPUT</b>                  |               |        |
| <b>RUNTIME (hours/min)</b>           |               | 32h    |
| <b>BEAM DISTANCE (meters)</b>        |               | 144m   |
| <b>PEAK BEAM INTENSITY (candela)</b> |               | 5189cd |
| <b>WATER RESISTANT</b>               |               |        |

**Approvals**

**IECEx** - ITS11.0023 Ex ia IIC T4 Ga (Energizer E93), 145°C (Duracell MN14)

**ETLus** - Class I II III Div. 1 Groups ABCDFG Operating Temp. T4 (Energizer E93), 145°C (Duracell MN1400), T3 (Panasonic LR14)