

NSYS3D4315P

Spacial S3D plain door with mount.plate.
H400xW300xD150 IP66 IK10 RAL7035.



Main

Range	Spacial
Product name	Spacial S3D
Device application	Multi-purpose
Product or component type	Compact enclosure
Enclosure nominal height	400 mm
Enclosure nominal width	300 mm
Enclosure nominal depth	150 mm
Door type	Plain
Mounting plate description	Plain
Type of gland plate	Standard
Installation accessory type	Wall-mounting
Device composition	Body 1 Mounting plate 1 Door with lock 1 Cable gland plate 1

Complementary

Variant particularity	Gutter-shaped front rail double sheet thickness Single piece body
Number of doors	1 front face
Door opening	Reversible 120 °
Lock type	3 mm double-bar lock
Accessibility for operation	Front
Removable parts	Door by hinges Cable gland plate by screws Mounting plate by fixing element
Material	Galvanised steel for mounting plate Steel for enclosure
Surface finish	Epoxy-polyester powder enclosure
Colour	Grey RAL 7035 enclosure :
Standards	IEC 62208
Product certifications	BV CUL DNV GL LR UL

Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty period	18 months
-----------------	-----------
