

TradeMaster®/Spec Grade 15A Duplex GFCI, White

1595W



From the innovator of the product category, comes a full range of Pass & Seymour GFCI receptacles to enhance safety, shorten installation times and increase productivity on the jobsite. With high-impact-resistant, thermoplastic construction, our spec-grade GFCI are the most durable GFCI available.

features & benefits

- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles. FSUL Listed (Federal Specification WC596). Trip indicator light (red LED).
- Side or internal screw-pressure-plate back wire with #10 – #14 AWG solid or stranded copper wire.
- Two back wire holes per terminal. Ground screw has a back wire clamp for easy installation.
- 1/4" thinner than competitors' GFCIs; leaves more room for wires in the box. Extra-long strap.
- Button colors match the device face. Dual-direction test and reset buttons. Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate. Tri-drive screws.
- GFCIs with Auto-Ground assure a positive ground to metal box.
- 10kA short circuit rating.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: White
Available Colors: White, ivory, light almond, red, brown, black, gray
Type: GFCI Receptacle
Style: Decorator

Listing Agencies/Third Party Information

RoH S: No
CSA Standard: C22.2 No. 42, 144
CUL Listing No: E42190
cULus: Yes
cUL Standard: Yes
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: UL498
UL Listed: Yes
UL Standard: Yes
UN SPS C: 39121614

Dimensions

Depth U S: 0.98"
Height U S: 4.2"
Length U S: 4.20"
Width U S: 1.72"

Technical Information

Amps: 15A
NEMA Configuration Number: 5-15R
NEMA Rating: WD-1, WD-6
Volts: 125V
Volts A C: 125
Grade Type: Specification

Buy American Act Compliance

Country of Origin: CHINA
Buy American Act Status: No