






REV	DESCRIPTION	DATE
-----	-------------	------

NOTE:

1. MAXIMUM ELECTRIC CURRENT:

A.W.G.	16	14
AMP.	10	15

15 AMPERE
2. MAXIMUM ELECTRICAL RATING:
125°C 300 VOLTS MAX.
3. INSULATION MATERIAL: PC
4. INSULATION COLOR: BLUE
5. TERMINAL MATERIAL: BRASS
6. WIRE RANGE: 16-14A.W.G. (1.5-2.5mm²)
7. TERMINAL THICKNESS: 0.4mm

Tolerance Unless Otherwise Specified	
0 >	mm ±
>	mm ±
>	mm ±
>	mm ±
ANGLE	° REF ±
	° ±
	° ±

NAME	PC-INSULATED PIGGY BACK DISCONNECTORS				UNIT	mm	
PART NO.	PBDNI2-250	MATERIAL				APPROVE	
NUMBER	TZV-102	SCALE	SHEET	PAGE	CHECKED		
DATE	09/07/2005	3 : 1	1-0	1 OF 1	DRAWN		