

CLAMP METERS

AC Digital Clamp Meter

NEW

- Tear drop shaped jaws for ease of use in crowded cable areas and other tight places.
- Sleep function to save battery.
- Data hold function.
- Digital display with maximum 4000 counts.

Specifications



MODEL 2007A

AC A	400/600A
AC V	400/750V
Ω	400 Ω /4k Ω
Continuity	buzzer sounds below 50 \pm 35 Ω
Conductor Size	\varnothing 33mm max.
Safety Standard	IEC61010-1 CAT. III 300V IEC61010-1 CAT. II 600V IEC61010-1 CAT. I 1000V IEC61010-2-031, IEC61010-2-032
Power Source	R03(1.5V) \times 2
Dimensions	195(L) \times 78(W) \times 36(D)mm
Weight	260g approx.

AC Digital Clamp Meter, from 0 to 2000A

NEW



**MODEL
2002PA**

- Tear drop shaped jaws for ease of use in crowded cable areas and other tight places.
- Terminal cover to avoid the use of incorrect terminal.
- PEAK function to measure current peak.

● Specifications

AC A	400/2000A
AC V	40/400/750V
DC V	40/400/1000V
Ω	400 Ω /4k/40k/400k Ω
Continuity	400 Ω
Output Voltage	400/2000A DC400mV/200mV
Conductor Size	\varnothing 55mm max.
Safety Standard	IEC61010-1 CAT. III 600V IEC61010-1 CAT. II 1000V IEC61010-2-031, IEC61010-2-032
Power Source	R6P(AA) (1.5V) \times 2 Approx. 150 hours in continuous use
Dimensions	247(L) \times 105(W) \times 49(D)mm
Weight	470g approx.