




- 1 CONTINUOUS STRIP ON REELS.
- 2 FOREIGN PRODUCTION ONLY.
- 3 0.002032 [.000080] MIN TIN PLATE.
- 4 0.000381 [.000015] MIN GOLD PLATE OVER 0.000762 [.000030] MIN NICKEL UNDERPLATE.
- 5 0.003810 [.000150] MIN NICKEL PLATE.
- 6 WIRE BARREL TO ACCEPT #22-#18 AWG STRANDED LEAD WIRE.
- 7 INSULATION BARREL ACCEPTS 2.16-3.18 [.085-.125] DIA INSULATION.

OBSOLETE	- 5	2	42581-4
OBSOLETE	4	-	42581-3
	- 3		42581-2
OBSOLETE	NONE		42581-1
FINISH		PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN MICHAEL S. FEHER 21JUL1999	AMP AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK DON DECKER 23JUL1999		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DON DECKER 23JUL1999	NAME RECEPTACLE, SHUR PLUG, 3.96 [.156] DIA	
0 PLC ±- 1 PLC ±- 2 PLC ±0.25 [.010] 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH SEE TABLE		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		
MATERIAL 4M BRASS		SIZE A2		RESTRICTED TO -
		CAGE CODE 00779		REV J
		DRAWING NO C- 42581		
		SCALE 5:1		
		SHEET 1 OF 1		
		CUSTOMER DRAWING		