

Datasheet

## **RS Pro VF White Flexible slot Cable Trunking Slotted Flexible Panel Trunking, W30 mm x, L500mm**

RS Stock No: **598-614**



### **Product Details**

RS Pro flexible slot cable trunking panel in white colour, measures 500 mm long and 30 mm wide. This polypropylene flexible slotted trunking panel with strong self adhesive backing, assist installation. The trunking panel has a round shape that possesses low flammability, halogen free and self extinguishing in accordance with UL94-V1 standard. The base has additional slots to accept further fixing if required (F.C. 50 mm) with a temperature range of -20 to +70°C.



ENGLISH

### Specifications:

Colour	White
Fire Behaviour	Flame Retardant, Low Smoke Density, Self-Extinguishing, Halogen Free
Length	0.5 m
Material	PP
Slot Type	Flexible
Standards Met	UL 94 V-1
Trunking/Chain Type	Slotted Flexible Panel Trunking
Width	30 mm
Temperature Range	-20 to +70°C