

Capacitor, film, 100 uF, +/-10% Tol, -40/+85C, Power Electronic

Dimensions (mm)

ID	Dimension	Tolerance
D	84	+/-0.5
L	40	+/-2
S	45	+/-1
LL	20	nom
F	10	nom

Specifications

Manufacturer:	KEMET
Brand:	Arcotronics
Capacitance:	100 uF
Temperature Range:	-40/+85C
Voltage:	600V
Tolerance:	+/-10%
Application:	Power Electronic
Body Type:	Vertical Can Std Profile
Construction:	Non-inductive
Lead Type:	Screw Terminal
Lead Specification:	M8
Mounting Type:	Bolt:m12
Maximum dVdT:	30v/us
Package Kind:	Bulk