



Sample photo

**Order symbol:** ALN 234018  
**Product nbr:** 7811410  
**Description:** Enclosure  
**Remarks:** Aluminium

**EAN:** 6418074016225  
**El. number:**  
**Finland:** 3420002  
**Electric No.** 8212045813  
**Denmark:**  
**Electric No. Sweden:** 7811410

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

| Dimensions:                  |                 |     |     | Accessories:                                  |                            |
|------------------------------|-----------------|-----|-----|-----------------------------------------------|----------------------------|
| mm:                          | 401             | 230 | 180 | ARH 40                                        | DIN-35 Mounting rail       |
| inch:                        | 15.8            | 9.1 | 7.1 | MRS 28541                                     | Wall fastening lug (2 pcs) |
|                              |                 |     |     | PH A & AH A/B                                 | Hinge set                  |
| Materials:                   |                 |     |     | Rating:                                       |                            |
| Material:                    | Aluminium       |     |     | Ingress Protection (EN 60529): IP66/IP67/IP68 |                            |
| Base colour:                 | RAL 7001        |     |     | Impact Resistance (EN 62262): IK08            |                            |
| Cover screws material:       | Stainless steel |     |     | NEMA Class: NEMA 1, 4, 4X, 12, 13             |                            |
| Cover colour:                | RAL 7001        |     |     |                                               |                            |
| Temperatures:                |                 |     |     |                                               |                            |
| Temperature °C (short term): | -50 ... 140 °C  |     |     |                                               |                            |
| Temperature °C (continuous): | -50 ... 80 °C   |     |     |                                               |                            |
| Temperature °F (short term): | -60 ... 285 °F  |     |     |                                               |                            |
| Temperature °F (continuous): | -60 ... 175 °F  |     |     |                                               |                            |
| Accessories:                 |                 |     |     |                                               |                            |
| AM 2340                      | Mounting plate  |     |     |                                               |                            |

ALU 401x230x110-180

