

# Power Commander PDU/120V /40A/split-phase (2 x 20A)/18 pcs 5-20R O/L remote ammeter

4B43B2-2-RAM



## features & benefits

Two circuits with two 20A resettable circuit breakers and two lighted remote LCD digital ammeters. Eighteen 20A outlets with T-slots, black housing. 12' [3.6m] cord. Length 54" [1.4m]. Includes two (2) 7' [1.2m] patch cables, two (2) remote displays, and one (1) rack mountable faceplate.



## specifications

### Technical Information

Amps: 40  
Mounting: 0U  
Rated Voltage: 120V  
Number Of Circuits: 2  
Receptacle Type: NEMA  
Network Monitoring: No  
Number Of Outlets: 18

### Buy American Act Compliance

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant