



ENGLISH

Datasheet

RS Pro Twisted Steel Abrasive Cup Brush, 12500rpm

RS Stock No: **831-028**



Product Details

RS Pro twisted abrasive cup brush with steel bristle, is perfect for more aggressive cleaning jobs than standard crimped cup brushes. It is perfect for use on standard angle grinders.

Features and Benefits

- 12500 rpm maximum safe speed
- Stainless steel bristle construction
- Arbor fixing type
- 20 mm long bristle



ENGLISH

Specifications:

Bristle Material	Steel
Fixing Type	Arbour
Bristle Length	20 mm
Face Width	65 mm
Fixing Size	M10 x 1.25
Maximum Safe Speed	12500 rpm
Bristle Type	Twisted
Number of Pieces	10
Suitable For	Roughening, Deburring, Planning, Edge Honing, Structuring, Descaling/Paint Stripping & Weld Seams