

Interface module - VIP-2/PT/FLK14/LED - 2904249


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE module, with push-in connection and flat-ribbon cable connector, for mounting on NS 35 rails, with pin strip and short and long locking latches for socket strips, 14-pos., with LED



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 813600
Weight per Piece (excluding packing)	111.6 g
Custom tariff number	85369010
Country of origin	United States
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width	41.9 mm
Height	72.1 mm
Depth	56 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. permissible operating voltage	24 V DC
Max. perm. current (per branch)	1 A
Number of positions	14
Status display	LED
Mounting position	any
Standards/regulations	IEC 60664

Interface module - VIP-2/PT/FLK14/LED - 2904249

Technical data

General

	DIN EN 50178
	IEC 62103
Pollution degree	2
Surge voltage category	II

Connection data for connection 1

Connection name	PCB connection
Connection method	Push-in connection
Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max.	14
Stripping length	8 mm

Connection data for connection 2

Connection name	Flat-ribbon cable connection
Number of connections	1
Connection method	IDC/FLK pin strip (2.54 mm)
Number of positions	14

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421

Interface module - VIP-2/PT/FLK14/LED - 2904249

Classifications

UNSPSC

UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Approvals

Approvals


Approvals


CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized


Ex Approvals

Approvals submitted

Approval details

CSA 	
mm ² /AWG/kcmil	26-14
Nominal current I _N	1 A
Nominal voltage U _N	24 V

UL Recognized 	
mm ² /AWG/kcmil	26-14
Nominal current I _N	1 A

cUL Recognized 	
mm ² /AWG/kcmil	26-14
Nominal current I _N	1 A

EAC

Interface module - VIP-2/PT/FLK14/LED - 2904249

Approvals

cULus Recognized  US

Accessories

Accessories

System cable

Cable - FLK 14/EZ-DR/ 30/KONFEK - 2295729



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 0.3 m

Cable - FLK 14/EZ-DR/ 50/KONFEK - 2288901



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 0.5 m

Cable - FLK 14/EZ-DR/ 100/KONFEK - 2288914



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 1 m

Cable - FLK 14/EZ-DR/ 150/KONFEK - 2288927



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 1.5 m

Interface module - VIP-2/PT/FLK14/LED - 2904249

Accessories

Cable - FLK 14/EZ-DR/ 200/KONFEK - 2288930



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 2 m

Cable - FLK 14/EZ-DR/ 250/KONFEK - 2288943



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 2.5 m

Cable - FLK 14/EZ-DR/ 300/KONFEK - 2288956



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 3 m

Cable - FLK 14/EZ-DR/ 350/KONFEK - 2288969



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 3.5 m

Cable - FLK 14/EZ-DR/ 400/KONFEK - 2288972



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 4 m

Interface module - VIP-2/PT/FLK14/LED - 2904249

Accessories

Cable - FLK 14/EZ-DR/ 450/KONFEK - 2290847



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 4,5 m

Cable - FLK 14/EZ-DR/ 500/KONFEK - 2290834



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 5 m

Cable - FLK 14/EZ-DR/ 550/KONFEK - 2290850



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 5,5 m

Cable - FLK 14/EZ-DR/ 600/KONFEK - 2290863



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 6 m

Cable - FLK 14/EZ-DR/ 800/KONFEK - 2299563



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 8 m

Interface module - VIP-2/PT/FLK14/LED - 2904249

Accessories

Cable - FLK 14/EZ-DR/1000/KONFEK - 2299576



Round cable set, with two 14-pos. socket strips (1:1 connection), for connecting 8 channels, cable length: 10 m

Cable - FLK EZ-DR.../.../... - 2295059



Round cable, with preassembly, not shielded, variable cable length

Cable - FLK 14/EZ-DR/ 50/KONFEK/S - 2296977



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 0.5 m

Cable - FLK 14/EZ-DR/ 100/KONFEK/S - 2296980



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 1 m

Cable - FLK 14/EZ-DR/ 150/KONFEK/S - 2296993



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 1.5 m

Interface module - VIP-2/PT/FLK14/LED - 2904249

Accessories

Cable - FLK 14/EZ-DR/ 200/KONFEK/S - 2297002



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 2 m

Cable - FLK 14/EZ-DR/ 300/KONFEK/S - 2299013



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 3 m

Cable - FLK 14/EZ-DR/ 400/KONFEK/S - 2299026



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 4 m

Cable - FLK 14/EZ-DR/ 600/KONFEK/S - 2299039



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 6 m

Cable - FLK 14/EZ-DR/ 800/KONFEK/S - 2299042



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 8 m

Interface module - VIP-2/PT/FLK14/LED - 2904249

Accessories

Cable - FLK 14/EZ-DR/1000/KONFEK/S - 2299055



Assembled shielded round cable, with two 14-pos. female connectors (1:1 connection), for connecting 8 channels, length: 10 m

Cable - FLK EZ-DR-S.../.../... - 2295046



Round cable, with preassembly, shielded, variable cable length

Drawings

Circuit diagram

