



## Wall Fans

### ARTIC - 405 PRC

Wall fans ARTIC series have 3 speeds and timer  
The PRC 405 ARTIC mode incorporates remote control and breeze and evening functions.

#### Function breeze

The fan alternately different speeds simulating a natural breeze. in Figure 1 shows the operating cycle as a function of the selected speed.

#### Night Function

difetentes fan cycles alternating function  
listed below according breeze



PRC 405 ARTIC  
remote control

Model	ARTIC-405 PRC
Voltage (V)	230
Frecuencia (Hz)	50
Nominal power (W)	50
Air flow (m3/h)	4.225/3.403/2.530
Maximum air output speed (m / sec)	3,8
Maximum sound power level (dB (A))	55
Adjustable timer	1 a 8 h.
Number of speeds	3
Remote control	•
Tilting head	•
Fuo head selector / oscillating	•
Security fence	•
Motor with thermal protection	•
Color	Gris
Weight (kg)	5
Propeller Ø (mm)	400
Cale length (mm)	1.500
Height (mm)	560
Barcode	8413893652843