





LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
J	—			変更	
		K		OBSOLETE 4--2, 9--1	07JAN09
				ECR-09-000161	TS
					KB



OBSOLETE	SELECTIVE-TIN (MATTE)	SELECTIVE TIN (BRIGHT) × 14 SELECTIVE GOLD × 2	3, 4	BLACK	2-5175615-2
	SELECTIVE-TIN	PRE-TIN	—	BLACK	9-175615-2
OBSOLETE	SELECTIVE-TIN	PRE-TIN	—	NATURAL	9-175615-1
OBSOLETE	SELECTIVE-TIN × 14	SELECTIVE GOLD × 2	8, 16	BLACK	4-175615-2
	TIN-LEAD	SELECTIVE GOLD × 2	8, 16	BLACK	3-175615-2
OBSOLETE	PRE-TIN × 14	SELECTIVE GOLD × 2	3, 4	BLACK	2-175615-2
	TIN-LEAD	SELECTIVE GOLD × 2	—	BLACK	175615-3
OBSOLETE	SELECTIVE-TIN (MATTE)	SELECTIVE-TIN (BRIGHT)	—	BLACK	175615-2
	PRE-TIN	PRE-TIN	—	WHITE	175615-1
OBSOLETE	SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	GOLD PLATED CIRCUIT NO 金めっき回路番号	COLOR 色	PART NUMBER 製品型番
	CONTACT FINISH コンタクト仕上		3		

- THE MATING PLUG HSG. PART NUMBER ; 174909, 175966
- RECOMMENDED MOUNTING SCREW 3mmDIA
6mmLENGTH (MAX) PAN HEAD, CLASS
2 TAPPING SCREW SPECIFIED IN JIS
B1115, B1122 (TIGHTENING TORQUE ; 39.2N-cm MAX)
- CIRCUIT NUMBER (SEE ABOVE)

- 嵌合相手ハウジング ; 174909, 175966
- 推奨取付ネジ ; JIS B1115, B1122 タッピングネジ、M3X6
ナベ2種 (締付トルク ; 39.2N-cm 以下)
- 回路番号 ; 上図参照のこと

GENERAL TOLERANCE	
0<*i 10 : ±0.2	
10<*i 30 : ±0.25	
30<*i 100 : ±0.3	
角 度 : ±3°	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.KADOSAKI 13OCT05	Tyco Electronics Corporation Kawasaki, Japan	
		CHK T.SHINOHARA 13OCT05		
		APVD K.BETSUI 13OCT05	NAME 名称	
		PRODUCT SPEC 製品規格	16POS CAP HOUSING ASSY 040 SERIES MULTI-LOCK I/O CONNECTOR MK-II	
		APPLICATION SPEC 取付適用規格		
		WEIGHT	SIZE A3	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C-175615	RESTRICTED TO —
			SCALE 尺度 2:1	SHEET 1 OF 1
				REV K