

Project..... Comments.....

Fixture Type..... Prepared By.....

**Product Description:**

Rotatable end caps. SMD LEDs. RA >80. Impact resistant frosted polycarbonate tube covers the aluminium heatsink. High power factor >0.90. Suitable for use at -20° to +40°C. 1kV surge protection. Beam 120°. Non-dimmable. Voltage range 100-240V. Life to 70% lumen maintenance - 40,000 hours. 5 Year guarantee.

**Product Image & Dimensions:**



Overall Diameter 30 mm  
Overall Length 1500 mm

**Product Specifications:**

- Lamp Type: T8
- Lamp Base: G13
- Input Voltage (Min): 100 V
- Input Voltage (Max): 240 V
- Input Voltage Type: AC
- Dimmable: No
- Beam Angle: 120 °
- Lifespan: 40000 hrs
- No. of LEDs: 324
- Overall Diameter: 30 mm
- Overall Length: 1500 mm
- Guarantee: 5 Years

**Compliance & Approvals:**



**SKU Table and Ordering:**

SKU Code	Wattage	Colour Temperature	Lumens	EAN	Qty
AU-XT81524FR/40	24 W	4000 K	2150 lm	5055155482237	<input type="text"/>
AU-XT81524FR/65	24 W	6500 K	2000 lm	5055155482244	<input type="text"/>

**Warranty:**

For available warranty information for this product, please visit:

[http://gb.auroralighting.com/Products/Indoor-Luminaires/Fire-Rated-Downlighting/MR16-Fire-Rated-Downlights/12V-MR16-Aluminium-Adjustable-Recessed-Baffle-\(1\).aspx](http://gb.auroralighting.com/Products/Indoor-Luminaires/Fire-Rated-Downlighting/MR16-Fire-Rated-Downlights/12V-MR16-Aluminium-Adjustable-Recessed-Baffle-(1).aspx)

**UK Sales**

16 Alban Park  
Hatfield Road, St. Albans  
United Kingdom  
PH: +44 (0) 1727 83 66 11  
FX: +44 (0) 1727 83 66 22

**UK Distribution**

Apex Park, 6 Little Burrows  
Burrowfields, Welwyn Garden City  
AL7 4SW  
United Kingdom  
PH: +44 (0) 1707 35 18 20  
FX: +44 (0) 1727 35 18 21