



Cordsets

euromast® Standard Duty Connectors, Unshielded, PVC

Features: •20-22 AWG • Available in 2-5 Conductor • High Grade Oil and UV Resistant PVC • Unshielded • Solid Nickel Plated Brass Coupling Nut • Gold Plated Contacts Standard • Fully Molded Plug Body • Many Cable Options Available



4-Pin, 250 VAC/300 VDC, 4 A

Mfr.'s Type		Cable Specs	Pinout	Application	Cable Length (Meters)*	Each
Straight	Right Angle					
Female						
RK 4.2T-2	WK 4.2T-2	2/20 AWG, Grey PVC, 105°C, 5.2 mm OD	1. N/C, 2. N/C, 3. Bn, 4. Bu	2-wire DC sensors	2	15.20
RK 4T-2	WK 4T-2	3/20 AWG, Grey PVC, 105°C, 5.2 mm OD	1. Bn, 2. N/C, 3. Bu, 4. Bk	3-wire DC sensors	2	15.20
RK 4T-2/S715	WK 4T-2/S715	3/20 AWG, Yellow PVC, 105°C, 5.2 mm OD	1. Bn, 2. N/C, 3. Bu, 4. Bk	3-wire DC sensors	2	15.20
RK 4.4T-2	WK 4.4T-2	4/22 AWG, Grey PVC, 105°C, 5.2 mm OD	1. Bn, 2. Wh, 3. Bu, 4. Bk	4-wire DC appl.	2	17.60
RK 4.43T-2	WK 4.43T-2	4/22 AWG, Yellow PVC, 105°C, 5.2 mm OD	1. Bn, 2. Wh, 3. Bu, 4. Bk	4-wire DC appl.	2	17.60
Male						
RS 4.2T-2	WS 4.2T-2	2/20 AWG, Grey PVC, 105°C, 5.2 mm OD	1. N/C, 2. N/C, 3. Bn, 3. Bu	2-wire DC sensors	2	15.20
RS 4T-2	WS 4T-2	3/20 AWG, Grey PVC, 105°C, 5.2 mm OD	1. Bn, 2. N/C, 3. Bu, 3. Bk	3-wire DC sensors	2	15.20
RS 4T-2/S715	WS 4T-2/S715	3/20 AWG, Yellow PVC, 105°C, 5.2 mm OD	1. Bn, 2. N/C, 3. Bu, 3. Bk	3-wire DC sensors	2	15.20
RS 4.4T-2	WS 4.4T-2	4/22 AWG, Grey PVC, 105°C, 5.2 mm OD	1. Bn, 2. Wh, 3. Bu, 3. Bk	4-wire DC appl.	2	17.60
RS 4.43T-2	WS 4.43T-2	4/22 AWG, Yellow PVC, 105°C, 5.2 mm OD	1. Bn, 2. Wh, 3. Bu, 3. Bk	4-wire DC appl.	2	17.60

5-Pin, 250 V, 4 A


Mfr.'s Type		Cable Specs	Pinout	Application	Cable Length (Meters)*	Each
Straight	Right Angle					
Female						
RK 4.5T-2	WK 4.5T-2	5/22 AWG, Grey PVC, 105°C, 5.7 mm OD	1. Bn, 2. Wh, 3. Bu, 4. Bk, 5. Gy	5-wire DC appl.	2	18.70
RK 4.5T-2/S715	WK 4.5T-2/S715	5/22 AWG, Yellow PVC, 105°C, 5.7 mm OD	1. Bn, 2. Wh, 3. Bu, 4. Bk, 5. Gy	5-wire DC appl.	2	18.70
Male						
RS 4.5T-2	WS 4.5T-2	5/22 AWG, Grey PVC, 105°C, 5.7 mm OD	1. Bn, 2. Wh, 3. Bu, 4. Bk, 5. Gy	5-wire DC appl.	2	18.70
RS 4.5T-2/S715	WS 4.5T-2/S715	5/22 AWG, Yellow PVC, 105°C, 5.7 mm OD	1. Bn, 2. Wh, 3. Bu, 4. Bk, 5. Gy	5-wire DC appl.	2	18.70

*Other cable lengths are available. Call for details & pricing.

picofast® Standard Duty Cordsets, Unshielded, PVC




Features: • High Grade Oil & UV Resistant PVC • Unshielded • Snap Lock or Threaded Coupling Nut • Available in 3, 4, and 6 Conductors • Solid Brass Coupling Nut • Gold Plated Contacts Standard • Fully Molded Plug Body • Many Cable Options Available. **Ratings:** 125 VAC/VDC, 4.0 A (3-wire); 125 VAC/VDC, 2 A (4-wire); 24 VDC, 1.0 A (6-wire).



Snap Lock 3, 4 and 6-Pin

Mfr.'s Type		Cable Specs	Pinout	Application	Cable Length (Meters)*	Each
Straight	Right Angle					
Female						
PKG 3Z-2	PKW 3Z-2	3/24 AWG, Yellow PVC, 105°C, 4.4 mm OD	1. Bn, 3. Bu, 4. Bk	Snap lock, 3-wire	2	12.20
PKG 4Z-2	PKW 4Z-2	4/26 AWG, Yellow PVC, 105°C, 4.4 mm OD	1. Bn, 2. Wh, 3. Bu, 4 Bk	Snap lock, 4-wire	2	14.00
PKG 6Z-2	PKW 6Z-2	6/26 AWG, Yellow PVC, 105°C, 4.5 mm OD	1. Bn, 2. Wh, 3. Bu, 4. Bk, 5. Gy, 6. Pk	Snap lock, 6-wire	2	17.10
Male						
PSG 3-2	-	3/24 AWG, Yellow PVC, 105°C, 4.4 mm OD	1. Bn, 3. Bu, 4. Bk	Snap lock, 3-wire	2	12.20
PSG 4-2	-	4/26 AWG, Yellow PVC, 105°C, 4.4 mm OD	1. Bn, 2. Wh, 3. Bu, 4 Bk	Snap lock, 4-wire	2	14.00
PSG 6-2	-	6/26 AWG, Yellow PVC, 105°C, 4.5 mm OD	1. Bn, 2. Wh, 3. Bu, 4. Bk, 5. Gy, 6. Pk	Snap lock, 6-wire	2	17.00



Threaded 3 and 4-Pin

Mfr.'s Type		Cable Specs	Pinout	Application	Cable Length (Meters)*	Each
Straight	Right Angle					
Female						
PKG 3M-2	PKW 3M-2	3/24 AWG, Yellow PVC, 105°C, 4.4 mm OD	1. Bn, 3. Bu, 4. Bk	Threaded, 3-wire	2	12.20
PKG 4M-2	PKW 4M-2	4/26 AWG, Yellow PVC, 105°C, 4.4 mm OD	1. Bn, 2. Wh, 3. Bu, 4 Bk	Threaded, 4-wire	2	14.00
Male						
PSG 3M-2	PSW 3M-2	3/24 AWG, Yellow PVC, 105°C, 4.4 mm OD	1. Bn, 3. Bu, 4. Bk	Threaded, 3-wire	2	12.20
PSG 4M-2	PSW 4M-2	4/26 AWG, Yellow PVC, 105°C, 4.4 mm OD	1. Bn, 2. Wh, 3. Bu, 4 Bk	Threaded, 4-wire	2	14.00

*Other cable lengths are available. Call for details and pricing.