

Interface module - FLKM 34/ZFKDS - 2302939

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)


Standard 1:1 FLK module, with spring-cage connection and flat-ribbon cable connector, no. of positions 34



The illustration shows a 40-position version



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 941444
Weight per Piece (excluding packing)	0.75 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Dimensions

Width	90 mm
Height	77 mm
Depth	51 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	< 50 V AC 60 V DC
Max. current carrying capacity per branch	1 A
Number of positions	34
Mounting position	any
Standards/regulations	IEC 60664 DIN EN 50178

Interface module - FLKM 34/ZFKDS - 2302939

Technical data

General

	IEC 62103
--	-----------

Connection data for connection 1

Connection name	PCB connection
Connection method	Spring-cage connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max.	12

Connection data for connection 2

Connection name	Flat-ribbon cable connection
Number of connections	1
Connection method	IDC/FLK pin strip (2.54 mm)
Number of positions	34

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Interface module - FLKM 34/ZFKDS - 2302939

Accessories

Accessories

System cable

Cable - FLK 34/EZ-DR/ 50/KONFEK - 2299479



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 0.5 m

Cable - FLK 34/EZ-DR/ 100/KONFEK - 2299482



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 1 m

Cable - FLK 34/EZ-DR/ 150/KONFEK - 2299495



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 1.5 m

Cable - FLK 34/EZ-DR/ 200/KONFEK - 2299505



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 2 m

Cable - FLK 34/EZ-DR/ 300/KONFEK - 2299518



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 3 m

Interface module - FLKM 34/ZFKDS - 2302939

Accessories

Cable - FLK 34/EZ-DR/ 400/KONFEK - 2299521



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 4 m

Cable - FLK 34/EZ-DR/ 600/KONFEK - 2299534



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 6 m

Cable - FLK 34/EZ-DR/ 800/KONFEK - 2299547



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 8 m

Cable - FLK 34/EZ-DR/1000/KONFEK - 2299550



Round cable set, with two 34-pos. socket strips (1:1 connection), cable length: 10 m

Cable - FLK EZ-DR.../.../... - 2295059



Round cable, with preassembly, not shielded, variable cable length

Drawings

Interface module - FLKM 34/ZFKDS - 2302939

Circuit diagram

