

TV8552 – TV8573 TVAC65000 – TVAC65501




D	Bedienungsanleitung
UK	User manual
FR	Manuel utilisateur
NL	Gebruikershandleiding
DK	Brugerhåndbog



Spezifikationen / Specification / Spécifications / Specificaties

						
TV8552	8.5 ~ 40 mm / F1.3	AUTO-IRIS	1/3": 34°~7° 1/4": 25°~5°	√	√	-
TV8553	2.8 ~ 12 mm / F1.3	MAN	1/3": 98°~24° 1/4": 74°~18°	√	√	-
TV8554	2.8 ~ 12 mm / F1.3	AUTO-IRIS	1/3": 98°~24° 1/4": 74°~18°	√	√	-
TV8555	2.9 ~ 8,2 mm / F1.0	MAN	1/3": 98°~35° 1/4": 69°~27°	√	√	-
TV8556	2.9 ~ 8,2 mm / F1.0	AUTO-IRIS	1/3": 98°~35° 1/4": 69°~27°	√	√	-
TV8572	5 ~ 50 mm / F1.3	MAN	1/3": 52°~6° 1/4": 39°~4°	-	√	-
TV8573	5 ~ 50 mm / F1.3	AUTO-IRIS	1/3": 52°~6° 1/4": 39°~4°	-	√	-
TVAC65000	2.8 ~ 12 mm / F1.3	AUTO-IRIS	1/3": 102°~24° 1/4": 74°~18°	√	√	√
TVAC65100	2.9 ~ 8.2 mm / F1.4	AUTO-IRIS	1/3": 98°~35° 1/4": 71°~26°	-	√	√
TVAC65501	3.1 ~ 8 mm / F1.2	AUTO-IRIS	1/3": 91°~35° 1/4": 68°~26°	√	√	√

Stift / PIN	Kabel / Cable / Câble / Kabels
1	Control (-)
2	Control (+)
3	Drive (+)
4	Drive (-)



ABUS Security-Center GmbH & Co. KG
Linker Kreuthweg 5
86444 Affing / Mühldhausen
www.abus-sc.com