

MATERIALS AND FINISHES

BODY: ZINC ALLOY
PLATED NICKEL

SOLDER TAIL(GROUND): COPPER OVER STEEL
PLATED TIN

SOLDER TAIL(SIGNAL): COPPER OVER STEEL
PLATED GOLD


CENTER CONTACT: PHOSPHOR BRONZE
PLATED GOLD

INSULATOR: POLYPROPYLENE (94V2)




BOARD LOCK: PHOSPHOR BRONZE
PLATED TIN

1/2-28 UNEF-2A

14.66
.577



NOTE:
LEADS MAY NEED TO BE
ADJUSTED TO FIT PCB



PCB LAYOUT
VIEWED FROM TOP

RECOMMENDED MOUNTING HOLE
PANEL THICKNESS: 5.40(.216) MAX
RECOMMENDED MOUNTING TORQUE:
1.36 N-m(12 INCH LBS) MAX

73171-4310	QTY (1) OF 73101-0040 IN SINGLE BAG WITH LABEL
73101-0040	BULK
PART NO.	PACKAGING

PS-89675-1030	PRODUCT SPECIFICATION
SPECIFICATION	DESCRIPTION

ORIGINALLY DRAWING BY WILSON 1996/03/01

A	B	C	REV	DESCRIPTION	CHG: ADD 73171-4310 EC NO: URF2012-0419 DRWN: BOMALLEY 2012/01/17 CHKD: AZR 2012/01/17 APPR: JWIENER 2012/01/24	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- ANGULAR ± 2 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE MM/IN DRAWN BY AROBERTSON DATE 2011/07/29 CHECKED BY SSS DATE 2011/07/29 APPROVED BY JWIENER DATE 2011/07/29	SCALE DESIGN UNITS METRIC	TITLE BNC JACK, R/A PCB 75 OHM BOARD LOCKS BNC-J/PCB, EWR-1149 MOLEX INCORPORATED	SHEET NO. 1 OF 1			
												DOCUMENT NO. SD-73101-0040		
													THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	