

Datasheet

Endoscope

Model: VCAMLDCOL

**TECHNICAL SPECIFICATIONS****CAMERA**

- Image sensor: 1/4 CMOS
- Viewing angle: 30°
- Lighting: 2 Leds
- Probe: 17mm
- Depth lighting in the dark: 1,5 m

MONITOR

- Display: 2.36 "color TFT-LCD
- Resolution: 480 * 240 pixels
- Power supply: 4 AA batteries (not included)
- Accessories: Mirror, Hook and Magnet

AREAS OF USE

- Internal Cracks / Reading the serial number within equipment / Recovery of lost items / Internal Control of pipes and wall cavity / Internal inspection of equipment / location of cables and pipes / Control and polls of connectors and sockets electrical

OPTIONAL

- EXTENSION TUBE - 1mt
Model: EXTVCAMLDCOL-IT

