

70415

Deck Scrub, waterfed, 270
mm, Very hard, White



This deck scrub has very effective water distribution and is ideal for use in heavily soiled areas such as abattoirs and meat processing plants.

Technical Data

Item Number	70415
Visible bristle length	24 mm
Material	Polypropylene Polyester Stainless Steel
Suitable for Food Contact (EU 1935/2004), ¹	Yes
Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice	Yes
FDA compliant raw material (CFR 21)	Yes
Meets the REACH Regulation (EC) No. 1907/2006	Yes
Use of Phthalates (e.g. Bisphenol A)	No
Is Halal compliant	Yes
Box Quantity	10 Pcs.
Quantity per Pallet (80 x 120 x 200 cm)	800 Pcs.
Quantity Per Layer (Pallet)	80 Pcs.
Box Length	380 mm
Box Width	290 mm
Box Height	175 mm
Length	270 mm
Width	75 mm
Height	95 mm
Gross Weight	0,414 kg
Net Weight	0,39 kg
Cubik metre	0,0023 M3
Recommended sterilisation temperature (Autoclave)	121 °C
Max. cleaning temperature (Dishwasher)	93 °C
Max. usage temperature (for food contact)	80 °C
Max usage temperature (non food contact)	100 °C
Min. usage temperature	-20 °C
Min. pH-value in usage concentration	2 pH
Max. pH-value in Usage Concentration	10,5 pH
GTIN-13 Number	5705020070419
GTIN-14 Number (Box quantity)	15705020070416
Commodity Code	96039099
Country of origin	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.