



Main

Range of product	Acti 9
Modular device name	IHP
Device short name	IHP 2c
Product or component type	Programmable digital time switch
Product compatibility	Mechanical compatibility with electrical distribution comb busbars
Number of channels	2
Battery type	Lithium
Function available	Automatic time changeover
Type of setting	Absence for holidays function
Language	Danish Dutch English Finnish French Norwegian Swedish

Complementary

Device application	Building
Measurement accuracy	+/- 1 s/day
Cycle duration	24 hours + 7 days
Maximum number of switchings	56
Minimum interval duration	1 min
Measurement accuracy	+/- 1 s/day 20 °C
Power consumption	7 VA
Maximum switching current	16 A - 250 V AC pf = 1 10 A - 250 V AC pf = 0.6
[Ue] rated operational voltage	230 V (+/- 10 %) AC 50/60 Hz
Display type	Backlit LCD
Battery life	6 yr
Backup time	6 years time and program saving
Product mounting	DIN rail
9 mm pitches	5
Colour tint	White(RAL 9003)
Width	45 mm
Height	85 mm
Depth	66 mm

Environment

Ambient air temperature for operation	-10...50 °C
IP degree of protection	IP20 B

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS	Compliant - since 0946 - Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - go to CaP for more details
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Available Download End Of Life Manual

Contractual warranty

Period	18 months
--------	-----------