

## Screw connection - WP-GA HF IP69K M25 BK - 3240913

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable gland, metric thread, IP68/69k protection, angled

The figure shows the WP-GA HF IP69K M10 BK version



### Key commercial data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 25 pc   |
| Minimum order quantity               | 25 pc   |
| GTIN                                 | <br>4 046356 710206 |
| Weight per Piece (excluding packing) | 31.02 g   |
| Custom tariff number                 | 39174000  |
| Country of origin                    | Germany   |
| Note                                 | Made to Order (non-returnable)  |

### Technical data

#### Dimensions

|                  |          |
|------------------|----------|
| Length (b)       | 57 mm    |
| Height           | 57 mm    |
| Width (a)        | 37 mm    |
| Diameter         | 34.00 mm |
| Outside diameter | 28.50 mm |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 115 °C |
| Degree of protection            | IP68/IP69K        |

#### General

|       |              |
|-------|--------------|
| Color | black        |
| Type  | Angled       |
|       | Outer thread |

# Screw connection - WP-GA HF IP69K M25 BK - 3240913

## Technical data

### General

|   |  |
|---|--|
| Components                              | free from silicone, halogen, and cadmium |
| Inflammability class according to UL 94 | HB                                       |
| Material                                | PA                                       |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27141131 |
| eCl@ss 4.1 | 27141131 |
| eCl@ss 5.0 | 27141131 |
| eCl@ss 5.1 | 27141120 |
| eCl@ss 6.0 | 27141120 |
| eCl@ss 7.0 | 27141120 |
| eCl@ss 8.0 | 27149109 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000897 |
| ETIM 4.0 | EC001178 |
| ETIM 5.0 | EC000441 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211812 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121411 |
| UNSPSC 12.01  | 39121411 |
| UNSPSC 13.2   | 39121411 |

## Approvals

### Approvals

---

#### Approvals

UL Recognized / VDE Zeichengenehmigung / LR

---

#### Ex Approvals

---


#### Approvals submitted


---

### Approval details

## Screw connection - WP-GA HF IP69K M25 BK - 3240913

### Approvals

UL Recognized 

VDE Zeichengenehmigung 

LR

### Accessories

#### Accessories

#### Corrugated pipe

Protective hose - WP-PA HF 28,5 BK - 3240684



Polyamide protective hose, inflammability class V0, UV resistant, 1 Pcs. / Pkt. = roll à 50 m

Protective hose - WP-PA HF-HB 28,5 BK - 3240842



Polyamide protective hose, inflammability class HB, UV resistant, 1 Pcs. / Pkt. = roll à 50 m

### Mounting material

Protective hose fixing bracket - WP-BASE A M25 - 3241085



Fixing bracket for protective sleeves, fixed with two screws