



ENGLISH

Datasheet

RS Pro Crimp Ring Terminal, M6 Stud Size, 4mm² to 6mm², 12AWG to 10AWG, Yellow

RS Stock No: **613-9413**



Product Details

RS Pro crimp ring terminal in yellow colour, has M6 stud size. It suits cables from 4 mm² to 6 mm² and 12 AWG to 10 AWG. A range of insulated crimp ring terminals are made from copper with flared vinyl or nylon (mini yellow) insulation. These insulated crimp ring wire connectors are colour coded for use with different wire sizes including mini yellow 0.2 - 0.5 mm² and are available with a variety of stud sizes.

Specifications:

Colour	Yellow
Contact Material	Copper
Contact Plating	Tin
Inner Ring Diameter	6.4 mm
Insulation Material	Vinyl
Insulation	Insulated
Maximum Wire Size (AWG)	10 AWG
Maximum Wire Size (mm ²)	6 mm ²
Minimum Wire Size (AWG)	12 AWG
Minimum Wire Size (mm ²)	4 mm ²
Outer Ring Diameter	12 mm
Overall Length	29.5 mm
Stud Size	M6
Thickness	1 mm
Wire Size	12 to 10 AWG
Temperature Rating	+75°C
Amperage Rating	35 to 50 A
Voltage Rating	600 V