



## -1. Torque tools

### -1.1. TORQUE TOOLS

- Electronic torque wrench
- Accuracy  $\pm 2\%$
- Visual, audio and vibration signal
- Reversible interchangeable heads (supplied with ratchet head)
- 60 teeth/6° action
- Memory capacity of 1 000 readings
- Automatic shut off and auto zero check on power up
- Data and set value retention during battery exchange
- Operating temperature range : 5°C - 42°C
- Storage temperature range : -10°C - 50°C
- PC software (Excel format), RS 232 serial link, supplied with software, cable and 3 AA batteries
- Ranges programmable in Nm,Lbf.ft.,Lbf.in.
- ISO 6789
- 89/336/EEC

## Measuring wrench

IZO-DM



<b>IZO-DM-30</b>	7314151846909	1	9x12	1/4"	3-30	2.21-22.13	26.6-265.5	6852-1	405	930
<b>IZO-DM-135</b>	7314151848200	1	9x12	3/8"	13.5-135	10-99.57	62-1195	7452-1	450	1000
<b>IZO-DM-200</b>	7314151846916	1	14x18	1/2"	20-200	14.75-147.50	177-1770	7852-1	535	1345
<b>IZO-DM-340</b>	7314151846923	1	14x18	1/2"	34-340	25.07-250.80	301-3009	7852-1	650	1525