


DHRB34C102M2FB

" # " indicates a package specification code.



< List of part numbers with package codes >
DHRB34C102M2FB

Shape



References

Packaging	Specifications	Minimum quantity
B	Packing in bulk	200

L size or outer diameter D (mm)	18.0 mm max.
T size	8.2 mm max.
Lead spacing F	12.7 ± 2.0mm
Lead diameter d	0.8 ± 0.05mm
Paint dripping e	4.0mm max.

Specifications

Capacitance	1000pF ± 20%
Rated voltage	15kVdc
Temperature characteristics (complied standard)	B(JIS)
Capacitance change rate	± 10%
Temperature range of temperature characteristics	-25 to 85
Operating temperature range	-25 to 100

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it ' s specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.