

Rittal – The System.

Faster – better – everywhere.

▶ PDU international, basic version – DK 7955.111

Date : Aug 27, 2014

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PDU international, basic version – DK 7955.111

created : 27.08.2014 build on www.rittal.com/uk-en



Product description

Description: Robust, compact basic power distributor for the IT environment. Thanks to the compact PDU, any IT rack may be easily equipped with a professional power distribution system. With the TS IT rack, assembly is even tool-free. The compact design allows simple assembly.

Material: Aluminium section, black anodised

**Protection category
IP to IEC 60 529:** IP 20

Packs of: 1 pc(s).

EAN: 4028177684928

**Customs tariff
number:** 85369085

Product features

Design: PDU Basic

Sockets: 24 / IEC 320 socket C13
4 / IEC 320 socket C19

To fit: Enclosure type: TS IT
TS 8
Height: 1400 mm

Infeeds: Qty.: 1
Phases per infeed: 1~

Length: 1115 mm

Length of connection cable:	3 m
Ambient conditions:	Operating temperature: 0°C...45°C
Circuit-breaker 16 A (qty.):	2
Type of electrical connection:	CEE
Rated current (max.):	32 A
Weight:	3.96 kg

Approvals

Declarations:  [Declaration of conformity \(DE\)](#)

Downloads

Data sheets:  [Technical details \(EN\)](#)

Documentation:  [Instructions \(EN, DE\)](#)
 [Instructions \(FR, EN, DE\)](#)