

**KEMET Part Number: R413R34705000M**  
(413R34705000M)

R41, Film, Metallized Polypropylene, Safety, 0.47 uF, 20%, 300 VAC (Y2), 1000 VDC, 110°C, Lead Spacing = 27.5mm



#### Dimensions

Parameter	Value
L	32mm +0.3mm
H	33mm +0.1mm
T	18mm +0.2mm
S	27.5mm +/-0.4mm
LL	25mm +2/-1mm
F	0.8mm +/-0.05mm

#### Packaging Specifications

<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	128

#### General Information

<b>Supplier:</b>	KEMET
<b>Series:</b>	R41
<b>Dielectric:</b>	Metallized Polypropylene
<b>Style:</b>	Radial
<b>Features:</b>	EMI Safety
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Qualifications:</b>	ENEC, UL, cUL, CQC

#### Specifications

<b>Capacitance:</b>	0.47 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage AC:</b>	300 VAC (Y2)
<b>Voltage DC:</b>	1000 VDC
<b>Temperature Range:</b>	-40/+110C
<b>Rated Temperature:</b>	110°C
<b>Dissipation Factor:</b>	0.30% 1KHz
<b>Insulation Resistance:</b>	63.8298 GOhms
<b>Max dV/dt:</b>	400 V/us
<b>Safety Class:</b>	Y2