

## Housing - HC-B 48-TFL-96/O1PG29G - 1675159

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Sleeve housing, for single locking latch, height 96 mm, without screw connection, 1x Pg29, straight cable entry

The illustration shows versions, sleeve housing with straight and lateral cable exit



### Key commercial data

Packing unit	1 pc
GTIN	 4 017918 149918
Weight per Piece (excluding packing)	693.0 g
Custom tariff number	85389099
Country of origin	Germany
Note	Made to Order (non-returnable)

### Technical data

#### Dimensions

Height	96 mm
Width	89 mm
Length	131.5 mm

#### Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Note	For contact inserts HC-B48, DD216, M
Type	B48
Housing type	Sleeve housing
Locking type	for single locking latch
No. of cable outlets	1
Cable exit	Straight

# Housing - HC-B 48-TFL-96/O1PG29G - 1675159

## Technical data

### General

Screw connection	none
Type of the screw connection	1x Pg29
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

# Housing - HC-B 48-TFL-96/O1PG29G - 1675159

## Approvals

---

### Approval details

EAC
-----

## Accessories

### Accessories

#### Full screw connection

Cable gland - G-INS-PG29-M68N-PNES-GY - 1411146



Cable gland, Cable gland material: Polyamide, External cable diameter 18 mm ... 25 mm, Shielding: No, Connecting thread: Pg29, Color: silver grey

---

Cable gland - G-INS-PG29-M68N-NNES-S - 1411176



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 18 mm ... 25 mm, Shielding: No, Connecting thread: Pg29, Color: silver

---

Cable gland - G-INSEC-PG29-M68N-NNES-S - 1411201



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 18 mm ... 25 mm, Shielding: Yes, Connecting thread: Pg29, Color: silver

---

### Plug for cable screw gland

Filler plugs - HC-BS-PG29 - 1674532



Filler plugs, for Pg screw connections, type Pg29

---

## Drawings

## Housing - HC-B 48-TFL-96/O1PG29G - 1675159

Dimensioned drawing

