

PSZROX-0830 - PSZROX

General Part Information

Product Description		PSZROX-0830
Article Number		33362
POPNut Type	i	PSZROX
Standard Bulk Pack Quantity		4,000

Geometry / Dimensions

Thread Size		M8
Body Type (open / closed)	i	Open
Body Features	i	Round
Body Length (mm)		16.00
Min. Grip Thickness (mm)		1.00
Max. Grip Thickness (mm)		3.00
Head Style	i	Reduced Head
Hole Diameter (mm)		10.60
Head Diameter (mm)		11.50
Head Thickness (mm)		0.80
Barrel Diameter (mm)		10.50

Material / Weight

Material	i	Steel
Weight per thousand (kg)		4.1

